


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/6/07	
A		REDRAWN	8/17/11	



SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold flash over Nickel underplate overall

Electrical:
Current rating: 3 Amp max
Contact resistance: 30 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 650 VAC for 1 minute
Environmental:
Lead free, RoHS compliant

Positions: 2 thru 10, 13
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

A

B

C

D

A

B

C

D



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DATE	

DRAWN	SS	11/6/07
CHECKED		
APPROVED		

TITLE	
.100 [2.54] GANGED MINI SHUNT, OPEN TOP	
.235 [5.98] HEIGHT, GOLD PLATED	
Phone: 908-687-5000 Fax: 908-687-5710	

SIZE	PART NO.	REV.
X	MSBG-XX-G	A
REF:	S00076T	SCALE: NTS
SHEET 1 OF 1		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

11/6/07

MSBG-XX-G

S00076T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MSBG-04-G](#) [MSBG-06-G](#) [MSBG-02-G](#) [MSBG-03-G](#) [MSBG-05-G](#)