


APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		CHANGED AMP TO 3A, WAS 1A	5/3/06	
B		REDRAWN	9/20/11	
C		UPDATE SPEC.	9/11/19	AY/BC



#### SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

G = Gold flash over Nickel underplate overall

T = Tin over Copper underplate overall

Electrical:

Current rating: 3 Amp max

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 650 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X           ± .10           ØX           ± .10 .XX          ± .020        Ø.XX          ± .015 .XXX       ± .015        Ø.XXX       ± .010			<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			TITLE		.100 [2.54] MINI SHUNT, HANDLE TOP .531 [13.50] HEIGHT	
DRAWN		SS	DATE		4/6/05	
CHECKED						
APPROVED						
REF: S00076T			SCALE: NTS		SHEET 1 OF 1	
SIZE X			PART NO. MSBH-X		REV C	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MSBH-G](#)