


Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		REVISED SHAPE	7/03/08	
B		REDRAWN	7/03/09	

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0  
Insulator color: Black  
Contacts: Phosphor Bronze  
Plating:  
G = Gold flash over Nickel underplate overall  
T = Tin over Copper underplate overall  
Electrical:  
Current rating: 3 Amp max  
Contact resistance: 30 mohms max  
Insulation resistance: 1000 Mohms min  
Dielectric withstanding voltage: 650 VAC for 1 minute  
Temperature Rating:  
Operating temperature: -55°C to +105°C  
Environmental:  
Lead free, RoHS compliant

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
.100 [2.54] MINI SHUNT, CLOSED TOP  
.335 [8.50] HEIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN				SS			
CHECKED				4/6/05			
APPROVED							
SIZE		PART NO.		SCALE		SHEET 1 OF 1	
X		MSDA-X		NTS		REV. B	
REF: S00076T							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MSDA-T](#)