



Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions + .021 [0.54]
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		Holes		TITLE	
.X	± .10	Ø.X	± .10	909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.XX	± .020	Ø.XX	± .015		
.XXX	± .015	Ø.XXX	± .010		
APPROVALS		DATE		.100 [2.54] WIRE HOUSING	
DRAWN	SS	4/8/05		SIZE	PART NO.
CHECKED				X	MTA-XX
APPROVED				REF:	SCALE: NTS
				SHEET 1 OF 1	REV. -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTA-09](#) [MTA-11](#) [MTA-02](#) [MTA-07](#) [MTA-10](#) [MTA-12](#) [MTA-06](#) [MTA-08](#) [MTA-03](#) [MTA-04](#) [MTA-05](#)