




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions + .016 [0.40]
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				TITLE .156 [3.96] WIRE HOUSING			
Holes				PART NO. MTB-XX			
.X ± .10				REV. -			
.XX ± .020				SCALE: NTS			
.XXX ± .015				SHEET 1 OF 1			
APPROVALS							
DATE							
DRAWN SS							
4/12/05							
CHECKED							
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTB-08](#) [MTB-09](#) [MTB-11](#) [MTB-07](#) [MTB-06](#) [MTB-02](#) [MTB-04](#) [MTB-05](#) [MTB-12](#) [MTB-03](#) [MTB-10](#)