




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/26/06	
A		REDRAWN	11/26/10	
B		UPDATED BORDER	12/20/19	SS



PART NUMBER	WIRE SIZE	INSULATOR COLOR	CONTACT RESISTANCE
MTD-A-XX-C-1	22 AWG	RED	10mΩ Max.
MTD-A-XX-D-1	24 AWG	WHITE	15mΩ Max.
MTD-A-XX-E-1	26 AWG	BLUE	20mΩ Max.
MTD-A-XX-F-1	28 AWG	GREEN	30mΩ Max.



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250V AC/DC max.

Current rating: 3 Amps max.

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 24

A = .100 [2.54] x No. of Positions

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ±.010			<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE		TITLE IDC MASS TERMINATION HOUSING .100 [2.54] SPACING, FEED THRU	
DRAWN		SS	7/26/06			
CHECKED						
APPROVED						
SIZE X		PART NO. MTD-A-XX-X-1			REV B	
REF: S00004T			SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTD-A-04-D-1](#) [MTD-A-07-D-1](#) [MTD-A-04-F-1](#) [MTD-A-10-F-1](#) [MTD-A-03-F-1](#) [MTD-A-09-E-1](#) [MTD-A-10-D-1](#) [MTD-A-02-D-1](#) [MTD-A-02-E-1](#) [MTD-A-07-E-1](#) [MTD-A-08-D-1](#) [MTD-A-02-F-1](#) [MTD-A-03-D-1](#) [MTD-A-08-E-1](#) [MTD-A-08-F-1](#) [MTD-A-03-E-1](#) [MTD-A-06-E-1](#) [MTD-A-04-E-1](#) [MTD-A-06-F-1](#) [MTD-A-05-D-1](#) [MTD-A-10-E-1](#) [MTD-A-06-D-1](#) [MTD-A-09-D-1](#) [MTD-A-09-F-1](#) [MTD-A-07-F-1](#) [MTD-A-05-E-1](#) [MTD-A-05-F-1](#)