



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		REDRAWN	11/29/10	



A = .156 [3.96] x No. of Positions

SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-2
Insulator color: White
Temperature Rating: Operating temperature: -40°C to +105°C

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

COVER FOR MTD-B

IDC MASS TERMINATION HOUSING

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HILES	HILES	HILES	SIZE	PART NO.	REV.	
.X ± .10	ØX ± .10	ØX ± .10	ØX ± .10	X	MTD-BC-XX	A	
.XX ± .020	ØXX ± .015	ØXX ± .015	ØXX ± .015				
.XXX ± .015	ØXXX ± .010	ØXXX ± .010	ØXXX ± .010				
APPROVALS				DATE			
DRAWN	SS	4/12/05					
CHECKED							
APPROVED							

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTD-BC-03](#) [MTD-BC-04](#) [MTD-BC-06](#) [MTD-BC-08](#) [MTD-BC-02](#) [MTD-BC-09](#) [MTD-BC-05](#) [MTD-BC-07](#) [MTD-BC-](#)
[10](#)