




APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-	7426	RELEASED	01/11/07	
A		REDRAWN	10/5/11	
B		UPDATE DRAWING	4/11/16	AY/JK
C		UPDATED SPEC.	9/12/18	HR/LW



RECOMMENDED P.C.B. LAYOUT

#### SPECIFICATIONS:

##### Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Hold Down: Brass, Matte Tin plated

##### Plating:

Gold over Nickel underplate on contact area

Gold flash over Nickel underplate on solder tails

##### Electrical:

Voltage rating: 150 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC for 1 minute

##### Temperature Rating:

Operating temperature: -40°C to +85°C

##### Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MM [INCHES]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 Ø.X ± .10  
.XX ± .020 Ø.XX ± .015  
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	BW	01/11/07
CHECKED		
APPROVED		

**ADAM TECH**  
INTERCONNECTS  
909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE			
TELEPHONE JACK, SMT, TOP ENTRY, 4P4C, SURFACE MOUNT			
SIZE	PART NO.	REV.	
X	MTJ-44HX1	C	
REF:	S00065T	SCALE:	NTS
SHEET 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTJ-44HX1](#)