





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/27/18	



RECOMMENDED PCB LAYOUT

# SPECIFICATIONS:

## Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Pantone P355C Green

Contacts: Phosphor Bronze

## Plating:

Round contact

Gold over Nickel underplate overall

Flat contact

Gold over Nickel underplate on contact area,

Tin over Nickel underplate on solder tails

## Electrical:

Voltage rating: 150 VAC max

Current rating: 1.5 Amp max

Contact resistance: 30 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 1,000 VAC

Temperature Rating:

Operating temperature: -40°C to +70°C

## Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X           ± .10           Ø.X           ±.10 .XX          ± .020          Ø.XX          ±.015 .XXX       ± .015          Ø.XXX       ±.010			<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE			
DRAWN		HR	9/27/18			
CHECKED		RC2	9/27/18			
APPROVED						
TITLE			MODULAR TELEPHONE JACK, 6P2C VERTICAL TOP ENTRY, PCB, NO PANEL STOPS, GREEN			
SIZE X		PART NO. MTJ-623X1-N-HT-P355C-A		REV. -		
REF: S00297T		SCALE: NTS		SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTJ-623X1-N-HT-P355C-A](#)