





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/16/09	
A		UPDATE DRAWING	8/15/18	AY/TY



#### SPECIFICATIONS:

##### Material:

Insulator: ABS, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Wire: 26 Awg, UL 1061

##### Plating:

Gold over Nickel underplate on mating area

##### Electrical:

Voltage rating: 125 VAC max

Current rating: 1.5 Amp

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC or 1,500 VDC for 1 minute

##### Temperature Rating:

Operating temperature: 0°C to +70°C

##### Environmental:

Lead free, RoHS compliant.



X	PLATING
0	15 $\mu$ in Gold
1	30 $\mu$ in Gold
2	50 $\mu$ in Gold

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	DY	6/16/09
CHECKED		
APPROVED		

**ADAM**  
**TECH**  
**INTERCONNECTS**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
WIRE LEADED TELEPHONE JACK, 616E,  
4P4C, 26AWG, STRIPPED, COLOR BLACK

SIZE X	PART NO. MTJP-616E-X-A1-1	REV. A
REF: S00005C	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTJP-616E-X-A1-1](#)