





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/4/04	
A		REDRAWN	10/23/12	



SECTION A-A

"X"	PLATING
X	Gold flash
U	15 µin Gold
W	30 µin Gold
G	50 µin Gold

SPECIFICATIONS:

Material: Insulator: Polycarbonate, rated UL 94V-0
Insulator color: Clear
Contacts: Phosphor Bronze
Plating: Gold over Nickel underplate on contact area
Electrical: Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Environmental: Lead free, RoHS compliant



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MODULAR TELEPHONE PLUG, 4P4C
STANDARD OVAL WIRE TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HOLES	DATE	APPROVALS	SIZE	PART NO.	REV.	
.X ± .10	ØXX ± .10			X	MTTP-44-X	A	
.XX ± .020	ØXXX ± .015						
.XXX ± .015	ØXXX ± .010						
DRAWN	SS	10/4/04					
CHECKED							
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTP-44-G](#)