








APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/25/20	



"X"	PLATING
X	Gold flash
U	15 µin Gold
W	30 µin Gold
G	50 µin Gold

SPECIFICATIONS:

Material:

Insulator: PC, Color: Clear

Contacts: Copper Alloy

Plating:

Gold over Nickel underplate on contact area

Electrical:

Voltage rating: 150 VAC rms

Current rating: 1.5 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage:

Contact to Contact: 1,000 VDC or AC Peak for 1 minute

Contact to Shield: 1,500 VDC or AC Peak for 1 minute

Mechanical:

Wire range: 21~23AWG, Ø1.35mm~1.45mm

Temperature Rating:

Operating temperature: -25°C to +55°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED MMANGLE 0~15 ± 0.15 15~30 ± 0.20 30~ ± 0.25 ± 1°		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
		TITLE MODULAR TELEPHONE PLUG, 8P8C, SOLID WIRE CONTACTS, CATE 8			
APPROVALS		DATE			
DRAWN	LH	9/25/20			
CHECKED	AY1	9/25/20			
APPROVED					
REF:		S00005C		SCALE: NTS	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTP-88-X-S-C8-A](#) [MTP-88-W-S-C8-A](#)