




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED DIM.	12/8/10	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: Nylon 66, rated UL 94V-2
Insulator color: White
Electrical: Operating voltage: 250 VAC max
Current rating: 3 Amps max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 20
A = .100 [2.54] x No. of Positions + .022 [0.57]
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		Holes	
.X ± .10	ØXX ± .10	TITLE	
.XX ± .020	ØXXX ± .015	.100 [2.54] WIRE HOUSING	
.XXX ± .015	ØXXX ± .010	SIZE PART NO. REV.	
APPROVALS		MTS-XX A	
DRAWN	SS	4/8/05	
CHECKED		X	
APPROVED		REF: SCALE: MTS SHEET 1 OF 1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTS-08](#) [MTS-07](#) [MTS-10](#) [MTS-03](#) [MTS-09](#) [MTS-02](#) [MTS-04](#) [MTS-06](#) [MTS-05](#) [MTS-12](#)