



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/29/11	
A		UPDATED DRAWING	12/26/14	HR/NP



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Copper underplate on solder tails

Electrical:

Operating voltage: 30 VDC max

Current rating: 1.0 Amp max.

Contact resistance: 50 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES			TITLE		
.X ± .10 .XX ± .020 .XXX ± .015			MINI USB, TYPE AB, SINGLE PORT RIGHT ANGLE, TRUE SMT, TAPE & REEL		
HOLES Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010			SIZE X		
APPROVALS			PART NO. MUSB-AB1-S-RA-TSMT-KT-T/R		
DRAWN			REV. A		
CHECKED			REF: S00126T		
APPROVED			SCALE: NTS		
			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MUSB-AB1-S-RA-TSMT-KT-T/R](#)