





Rev	AWO #	Description	Date	Appr
-		RELEASED	2/7/08	
A		REDRAWN	8/03/09	
B		REVISED SPEC.	1/16/12	

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT



**SPECIFICATIONS:**

**Material:**

Insulator: Hi-temp thermoplastic, glass reinforced,  
rated UL 94V-0

Insulator color: Black

Contacts: Brass

**Plating:**

Gold Flash over Nickel underplate on contact area,  
Tin over Copper underplate on PCB tails

**Electrical:**

Operating voltage: 30 VAC max

Current rating: 1 Amps max

Contact resistance: 50 Mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VAC for 1 minute

**Temperature Rating:**

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



**ADAM TECH**

909 Ratway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, RIGHT ANGLE  
PCB MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X	± .10	Ø.X	± .10	TITLE	MINI USB, TYPE B, 5PIN, RIGHT ANGLE	SIZE	PART NO.
.XX	± .020	Ø.XX	± .015	PHONE	908-687-5000	REF:	S00005C
.XXX	± .015	Ø.XXX	± .010	DATE	2/7/08	SCALE:	NTS
APPROVALS				SHEET 1 OF 1			
DRAWN	SS	2/7/08		REV. B			
CHECKED							
APPROVED							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MUSB-B5-S-RA-1-T/R](#) [MUSB-B5-S-RA-1](#)