

6

5

4

3






2

1

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|---------|------|
| - | | RELEASED | 7/13/12 | |

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: Brass, Nickel Plated
Plating:
Gold Flash over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Current Rating: 1.0 A AC/DC
Voltage Rating: 30 V AC/DC
Contact resistance: 50 Mohms max
Insulation resistance: 100 Mohms min
Dielectric withstanding voltage: 100 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +80°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM
TOLERANCES: EXCEPT AS NOTED
.XX ± 0.25
.XXX ± 0.20

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, VERTICAL, TRUE SMT

| APPROVALS | | DATE | TITLE | |
|-----------|----|---------|--------|---------------------|
| DRAWN | AY | 7/13/12 | SIZE | PART NO. |
| CHECKED | AH | 7/13/12 | X | MUSB-B5-S-VT-TSMT-1 |
| APPROVED | | | REF: | S00126T |
| | | | SCALE: | NTS |
| | | | SHEET | 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MUSB-B5-S-VT-TSMT-1](#)