




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/31/13	
A		ADDED & REVISED DIM.	8/19/13	
B		UPDATED DRAWING	8/30/16	HR/CH
C		UPDATED DIM.	8/17/18	AY/KC
D		UPDATED DESCRIPTION	8/24/18	AY/KC



PANEL THICKNESS	DIM " L "
.031 [0.80]	.945 [24.00]
.039 [1.00]	.969 [24.60]
.047 [1.20]	.992 [25.20]
.063 [1.60]	1.031 [26.20]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate overall

Electrical:

Rating: 15A, 125V (C-ULus)

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 3,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
					TITLE			
			APPROVALS		DATE		NEMA RECEPTACLE	
			DRAWN	AY	7/31/13			
			CHECKED	LW	7/31/13			
APPROVED			SIZE X	PART NO. NEMA-5-1-B	REV. D			
			REF: S00087C	SCALE: NTS	SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[NEMA-5-1-B](#)