







APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/19/05	
A		REVISED SHAPE & DIM.	2/18/14	AY/KW
B		CHG'D CONTACT MATERIAL TO BRASS	10/17/16	AY/KW
C		CHG'D MTL TO C2680, EH, Hardness: HV 183	11/24/16	AY/KW



SECTION A-A



#### SPECIFICATIONS:

##### Material:

Insulator: Nylon 66, rated UL94V-0

Insulator color: Black

Contacts: Brass, C2680, Level: EH, Hardness: HV 183, Tin plated

##### Electrical:

Operating voltage: (C-ULus) 125 VAC

Current rating: (C-ULus) 15 Amps max.

Insulation resistance: 100 Mohms min. @ 500 VDC

Dielectric withstanding voltage: 3,000 VAC for 1 minute

Recommended wire size: 14 AWG solid

##### Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	1/19/05
CHECKED		
APPROVED		

## ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE		
NEMA UNIVERSAL PANEL SNAP RECEPTACLE		
SIZE	PART NO.	REV.
X	NEMA-5-3	C
REF:	S00087C	SCALE: NTS
SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[NEMA-5-3](#)