


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/04/12	
A		UPDATE DRAWING	1/10/18	AY/RC1



RECOMMENDED PANEL CUT
R.020 [0.50]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate overall

Electrical:

Rating: 15A, 125V (C-ULus)

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 3,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	TW	12/04/12
CHECKED	YC	12/04/12
APPROVED		

**ADAM
TECH**
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
NEMA UNIVERSAL PANEL SNAP RECEPTACLE
HORIZONTAL WIRE

SIZE X	PART NO. NEMA-5-3-HW	REV. A
REF: S00087C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[NEMA-5-3-HW](#)