

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/8/20	

**SPECIFICATIONS:**

Material:

Housing: PBT, rated UL 94V-0, Color: Blue

Cap: PP, rated UL 94V-0, Color: White

Electrical:

Standards of IEC 61754-20, YD/T 1272.1-2003

Repeatability: 500 min times

Insertion loss: 0.2dB max

Interchangeability: 0.2dB

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.35	X.* ± 2°
.X ± 0.30	.X* ± 1°
.XX ± 0.25	.XX* ± 0.5°
.XXX ± 0.15	.XXX* ± 0.5°

APPROVALS		DATE
DRAWN	OW	9/8/20
CHECKED	JL	9/8/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE OPTICAL LC ADAPTERS, PC, DUAL ROW,
2*2 PORTS, SHORT EARS, WITH LC DUST CAP

SIZE X	PART NO. OPLB4SBNNC1NA	REV. -
REF: S00005C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[OPLB4SBNNC1NA](#)