




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/22/21	
A		UPDATE LABEL	7/19/21	WX/AC
B		UPDATE LABEL	1/12/24	WX/SL



SPECIFICATIONS:

Connector

P1: Power Adapter, W/Strain

P2: DC Plug, W/Strain Relief, AC PIN: Brass Nickel plated, 5.5*2.1*9.5mm
Overmold Color: Black PVC-45P

CABLE:

UL2468: 24AWG*2C 80°C, Jacket Color: Black

Electrical:

Input:

Voltage: 100Vac to 240Vac

Current: 1.5A Max. @ 100Vac input & max load

Frequency: 50Hz / 60Hz

Output:

Voltage: 24V

Current: 0.8A max.

Load Regulation: ±5%

Line Regulation: ±3%

Line Load Regulation—Output Rate: 24V, 0.8A

Insulation Resistance: 100 Mohms min @ 500VDC

Dielectric withstanding voltage (Hi-pot): 3,000V AC For 1 Minute

Leakage Current: 0.25mA max. @ 240V AC/50Hz

Temperature Rating:

Operating Temperature: 0°C to +45°C

Storage Temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



SEE SHT 2 OF 2 FOR PLUG TYPE OPTIONS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES	XX ±.10 .XX ±.020 .XXX ±.015	HOLES ØX ±.10 ØXX ±.015 ØXXX ±.010		
DRAWN	WX	3/22/21		
CHECKED	AC	3/22/21		
APPROVED			TITLE POWER ADAPTER TO DC PLUG, COLOR BLACK 24 VOLT, 0.8AMP, UL2468 24AWG	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			SIZE X	PART NO. PA-008-X
REF:			SCALE: NTS	SHEET 1 OF 2

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev


AWO #

Description


Date

Appr


SEE SHT 1 OF 2 FOR REVISION




US (NEMA 1-15) P/N: PA-008-1




AUSTRALIAN P/N: PA-008-4



EUROPEAN (Type C) P/N: PA-008-2



8HINA P/N: PA-007-5



UK / IRELAND P/N: PA-008-3

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN

WX

3/22/21

CHECKED

AC

3/22/21

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

 TITLE
 POWER ADAPTER TO DC PLUG, COLOR BLACK
 24 VOLT, 0.8AMP, UL2468 24AWG

SIZE

PART NO.

PA-008-X

REV.

B

REF:

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PA-008-1](#)