





APPROVED: _____

DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/23/21	
A		UPDATE DRAWING	4/27/21	WX/AC
B		UPDATE DRAWING	6/10/21	JJ



SPECIFICATIONS:

Material:

Case, cover & Chassis: PC, rated UL94V-0, Color: Black

AC Blades: Brass, Nickel plated

Electrical:

Input:

Voltage: 100Vac to 240Vac

Current: 0.4A Max. @ 100Vac input & max load

Frequency: 50Hz / 60Hz

Output:

Voltage: 5.0Vdc

Current: 3.0A max. (Current Range: 0 ~ 1.0A)

Load Regulation: ±5%

Insulation Resistance: 10 Mohms min @ 500VDC

Dielectric withstanding voltage (Hi-pot): 3,000V AC For 1 Minute

Leakage Current: 30mA max. @ 230V AC/50Hz

Temperature Rating:

Operating Temperature: 0°C to +45°C

Storage Temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	WX	3/23/21
CHECKED	AC	3/23/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		AC POWER ADAPTER, NEMA 1-15 TO USB TYPE A, 5V, 1 AMP, COLOR WHITE	
SIZE	PART NO.	REV.	
X	PA-010	B	
REF:	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PA-010](#)