





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/23/21	
A		UPDATE TITLE.	6/10/21	
B		UPDATE LABEL	7/19/21	WX/AC
C		UPDATE DESCRIPTION	4/11/23	SS



USB, TYPE C  
FEMALE



#### SPECIFICATIONS:

##### Material:

Case, cover & Chassis: PPHOX, rated UL94V-1, Color: white

AC Blades: Brass, Nickel plated

##### Electrical:

###### Input:

Voltage: 100Vac to 240Vac

Current: 0.5A Max. @ 100Vac input & max load

Frequency: 50Hz / 60Hz

###### Output Power:

Total Output: 18 Watts max.

PD Output: 5Vdc @ 3A

9Vdc @ 2A

12Vdc @ 1.5A

Load Regulation:  $\pm 7\%$

Line Regulation:  $\pm 7\%$

(Switching power supply adjust the PD output to match device connected)

Insulation Resistance: 50 Mohms min @ 500VDC

Dielectric withstanding voltage (Hi-pot): 3,000V AC For 1 Minute

Leakage Current: 0.25mA max. @ 240V AC/50Hz


##### Temperature Rating:

Operating Temperature:  $-10^{\circ}\text{C}$  to  $+40^{\circ}\text{C}$

Storage Temperature:  $-20^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

##### Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS  
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X $\pm .10$	$\varnothing$ .X $\pm .10$
.XX $\pm .020$	$\varnothing$ .XX $\pm .015$
.XXX $\pm .015$	$\varnothing$ .XXX $\pm .010$

DRAWN	WX	3/23/21
CHECKED	AC	3/23/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY  
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN  
PERMISSION FROM ADAM TECH

**ADAM  
TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
AC POWER ADAPTER, NEMA 1-15 TO USB TYPE C  
18W PD OUTPUT, COLOR WHITE

SIZE X	PART NO. PA-014	REV. C
REF:	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PA-014](#)