





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/2/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 10 mohms max. initial

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Mechanical:

Recommended PCB thickness: 0.063" (1.60mm)

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 02 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				Holes			
.X ± .10				Ø.X ± .10			
.XX ± .020				Ø.XX ± .015			
.XXX ± .015				Ø.XXX ± .010			
APPROVALS				DATE			
DRAWN				SS			
6/2/05							
CHECKED							
APPROVED							
TITLE				.100 [2.54] PCB CONNECTOR			
BOARD HOOKS, BOTTOM ENTRY							
SIZE				PART NO.			
X				PCE-C-XX			
REV.				REV.			
-				-			
SCALE: NTS				SHEET 1 OF 1			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PCE-C-05](#) [PCE-C-06](#) [PCE-C-09](#) [PCE-C-12](#) [PCE-C-03](#) [PCE-C-08](#) [PCE-C-11](#) [PCE-C-07](#) [PCE-C-10](#) [PCE-C-02](#)
[PCE-C-04](#)