




Rev	AWO #	Description	Date	Appr
-		RELEASED	10/5/04	

APPROVED: _____

DATE: _____ TITLE: _____

PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating: Gold Flash over Nickel underplate overall
Electrical: Current rating: 3 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions.
B = .100 [2.54] X No. of Spaces.
02 THRU 40 PINS AVAILABLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]			
TOLERANCES: EXCEPT AS NOTED		HOLD	
INCHES		HOLD	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	SS	10/5/04	
CHECKED			
APPROVED			

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710
PIN HEADER, SINGLE ROW, .100 PITCH
STRAIGHT, .235 MATING / .120 TAIL

SIZE	PART NO.	REV.
X	PH1-XX-UA-HT	-
REF:	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH1-02-UA-HT](#) [PH1-03-UA-HT](#) [PH1-16-UA-HT](#) [PH1-01-UA-HT](#) [PH1-04-UA-HT](#) [PH1-06-UA-HT](#) [PH1-05-UA-HT](#)