





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/4/05	
A		REVISED SPEC.	03/26/13	



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 3 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant

Positions: 1 thru 40
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH			
INCHES				909 Rahway Avenue, Union, NJ 07083			
Holes				Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØXX	± .10	TITLE .100 [2.54] SINGLE ROW PIN HEADER RIGHT ANGLE, LOW PROFILE, GOLD PLATED			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXXX	± .010				
APPROVALS				DATE			
DRAWN				SS			
CHECKED				4/4/05			
APPROVED				X			
SIZE				PART NO.			
X				PH1RB-XX-UA			
REV.				A			
REF:				S00039T			
SCALE:				NTS			
SHEET				1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH1RB-07-UA](#) [PH1RB-18-UA](#) [PH1RB-11-UA](#) [PH1RB-06-UA](#) [PH1RB-12-UA](#) [PH1RB-10-UA](#) [PH1RB-03-UA](#)
[PH1RB-04-UA](#) [PH1RB-01-UA](#) [PH1RB-09-UA](#) [PH1RB-16-UA](#) [PH1RB-13-UA](#) [PH1RB-02-UA](#) [PH1RB-05-UA](#) [PH1RB-](#)
[19-UA](#) [PH1RB-20-UA](#) [PH1RB-17-UA](#) [PH1RB-14-UA](#) [PH1RB-15-UA](#) [PH1RB-08-UA](#)