



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/19	
A		REDRAWN	5/22/24	JJ/TW
B		UPDATE SPEC.	10/16/24	LL1/AL



4.30mm Length



4.30mm Length
Positions: 01 thru 40 Unit:mm

ADAM P/N	Initial Height
PH2-3B-XX-MVS-4355-C1	5.5mm
PH2-3B-XX-MVS-4360-C1	6.0mm

5.30mm Length



5.30mm Length
Positions: 01 thru 40 Unit:mm

ADAM P/N	Initial Height
PH2-3B-XX-MVS-5365-C1	6.5mm
PH2-3B-XX-MVS-5370-C1	7.0mm
PH2-3B-XX-MVS-5375-C1	7.5mm
PH2-3B-XX-MVS-5380-C1	8.0mm

SPECIFICATIONS:

Material:

Insulator: PA46, rated UL 94V-0, Color: Black

Contacts: Brass

Spring: Stainless Steel

Plating:

Gold flash over Nickel underplate overall

Electrical:

Voltage rating: 12 Volts

Current rating: 3A max

Contact resistance @ working stroke: 50 mohms max Δ

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VRMS @ 60HZ

Mechanical:

Spring force: 70g $\pm$ 20g @ 1.0mm working stroke (4.30 & 5.30mm)

Full stroke: 1.40mm

Life test: 10,000 Cycles Min

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES
.X	$\pm .10$	$\varnothing X \pm .10$
.XX	$\pm .020$	$\varnothing XX \pm .015$
.XXX	$\pm .015$	$\varnothing XXX \pm .010$

DRAWN	OW	5/10/19
CHECKED	AC	5/10/19
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CUSTOM LENGTH TUBE DOUBLE ROW STRIPS
1.50MM INSULATOR HEIGHT, SOLDER CUP

SIZE X	PART NO. PH2-3B-XX-MVS-XXXX-C1	REV. B
REF: S00185C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH2-3B-10-MVS-5375-C1](#) [PH2-3B-20-MVS-4360-C1](#) [PH2-3B-06-MVS-4360-C1](#) [PH2-3B-08-MVS-5375-C1](#) [PH2-3B-02-MVS-4360-C1](#) [PH2-3B-20-MVS-5375-C1](#) [PH2-3B-02-MVS-5375-C1](#) [PH2-3B-10-MVS-4360-C1](#)