






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/25/19	
A		UPDATE DRAWING	8/1/19	LH/RC



RECOMMENDED PCB LAYOUT



PH2-3F-04-FVP-24415-C1

Insulator: PA46

SPECIFICATIONS:

Material:

Insulator: (PA9T or PA46) Hi-Temp Thermoplastic, rated UL 94V-0, Color: Black

Contacts: Copper Alloy

Plating:

3u" Gold over Nickel underplate overall

Electrical:

Voltage rating (Per Contact): 12 Volts

Current rating (Per Contact): 3A max

Contact resistance : 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 1,000 VRMS @ 60HZ

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MILLIMETERS
 TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.20	X° ± 2°
.X ± 0.15	.X° ± 0.5°
.XX ± 0.10	

APPROVALS		DATE
DRAWN	LH	7/25/19
CHECKED	RC	7/25/19
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710



TITLE
 CUSTOM LENGTH TUBE DOUBLE ROW STRIPS
 1.50MM INSULATOR HEIGHT, DIP LOADED

SIZE	PART NO.	REV.
X	PH2-3F-XX-FVP-24415-C1	A
REF: S00185C	SCALE: NTS	SHEET 1 OF 4



Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 4 FOR REVISION				

APPROVED: _____




DATE: _____ TITLE: _____






RECOMMENDED PCB LAYOUT



RECOMMENDED PCB LAYOUT



PH2-3F-06-FVP-24415-C1
Insulator: PA46



PH2-3F-08-FVP-24415-C1
Insulator: PA46

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.20	X° ± 2°
.X ± 0.15	.X° ± 0.5°
.XX ± 0.10	

APPROVALS		DATE
DRAWN	LH	7/25/19
CHECKED	RC	7/25/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	CUSTOM LENGTH TUBE DOUBLE ROW STRIPS 1.50MM INSULATOR HEIGHT, DIP LOADED
-------	---

SIZE X	PART NO. PH2-3F-XX-FVP-24415-C1	REV A
REF: S00185C	SCALE: NTS	SHEET 2 OF 4

6

5

4

3

2




1

APPROVED: _____

DATE: _____ TITLE: _____




Rev AWO # Description Date Appr

SEE SHT 1 OF 4 FOR REVISION



PH2-3F-10-FVP-24415-C1

Insulator: PA46



PH2-3F-12-FVP-24415-C1

Insulator: PA9T

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.20	X. ± 2°
.X ± 0.15	.X ± 0.5°
.XX ± 0.10	

APPROVALS		DATE
DRAWN	LH	7/25/19
CHECKED	RC	7/25/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CUSTOM LENGTH TUBE DOUBLE ROW STRIPS
1.50MM INSULATOR HEIGHT, DIP LOADED

SIZE	PART NO.	REV.
X	PH2-3F-XX-FVP-24415-C1	A
REF:	S00185C	SCALE: NTS
SHEET 3 OF 4		

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 4 FOR REVISION				

APPROVED: _____




DATE: _____ TITLE: _____






RECOMMENDED PCB LAYOUT



RECOMMENDED PCB LAYOUT



PH2-3F-16-FVP-24415-C1
Insulator: PA9T



PH2-3F-20-FVP-24415-C1
Insulator: PA9T

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.20	X° ± 2°
.X ± 0.15	.X° ± 0.5°
.XX ± 0.10	

APPROVALS		DATE
DRAWN	LH	7/25/19
CHECKED	RC	7/25/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	CUSTOM LENGTH TUBE DOUBLE ROW STRIPS 1.50MM INSULATOR HEIGHT, DIP LOADED
-------	---

SIZE X	PART NO. PH2-3F-XX-FVP-24415-C1	REV. A
REF: S00185C	SCALE: NTS	SHEET 4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH2-3F-08-FVP-24415-C1](#) [PH2-3F-20-FVP-24415-C1](#) [PH2-3F-04-FVP-24415-C1](#) [PH2-3F-06-FVP-24415-C1](#) [PH2-3F-10-FVP-24415-C1](#)