

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/19/18	



MATING ADAM PART: CA-ST6-PH2-254105-M

SPECIFICATIONS:

Electrical:

Rated Current & Voltage: 12VDC, 2A

Contact resistance: 50 mohms max

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED			<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
MM		ANGLE				
0~6 ± 0.05 6~30 ± 0.10 30~150 ± 0.15	± 1°					
APPROVALS			TITLE			
DATE			POGO PIN PCB CONN, 2.54MM PITCH			
DRAWN	HR	9/19/18	FEMALE, 2X3P, STRAIGHT, W/ PCB			
CHECKED	CK	9/19/18				
APPROVED						

SIZE	PART NO.	REV.
X	PH2-C25410-06-FVP	-
REF:	S00170C	SCALE: NTS
		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH2-C25410-06-FVP](#)