





Rev	AWO #	Description	Date	Appr
-		RELEASED	9/20/04	

APPROVED: _____

DATE: _____ TITLE: _____



A = .100 [2.54] X No. of Positions.
B = .100 [2.54] X No. of Spaces.

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max. Initial

Insulation resistance: 5000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: DUAL ROW PIN HEADER, .100" [2.54mm]
PITCH, TIN PLATED, 2 TO 80 PINS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				HOLE SIZES				DATE			
.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010	APPROVALS	DATE	SIZE	PART NO.
DRAWN	SS	9/20/04		CHECKED				APPROVED				REF:	SCALE: NTS	SHEET 1 OF 1	REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PH2-64-TA](#) [PH2-14-TA](#) [PH2-04-TA](#) [PH2-10-TA](#) [PH2-38-TA](#) [PH2-06-TA](#) [PH2-50-TA](#) [PH2-58-TA](#) [PH2-20-TA](#) [PH2-36-TA](#) [PH2-30-TA](#) [PH2-12-TA](#) [PH2-28-TA](#) [PH2-56-TA](#) [PH2-42-TA](#) [PH2-54-TA](#) [PH2-72-TA](#) [PH2-26-TA](#) [PH2-24-TA](#) [PH2-08-TA](#) [PH2-34-TA](#) [PH2-22-TA](#) [PH2-46-TA](#) [PH2-80-TA](#) [PH2-18-TA](#) [PH2-16-TA](#) [PH2-40-TA](#)