

6

5

4

3


2

1





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/18	



RECOMMENDED PCB LAYOUT



Mating with: CA-RA2-PHR-34113-M-WT
CA-ST2-PHR-202-M

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Pin: Brass, 10u" Gold plated over Nickel

Copper pipe: Brass, Nickel plated

Magnet: NdFeB

Electrical:

Rated Current & Voltage: 24VDC, 5A max

Contact resistance: 50 mohms max

Environmental:

Lead free, RoHS compliant.



<div>UNLESS OTHERWISE SPECIFIED</div> <div>ALL DIMENSIONS ARE MILLIMETERS</div> <div>TOLERANCES: EXCEPT AS NOTED</div> <div>MillimetersANGLE</div> <div>0~6 ± 0.05</div> <div>6~30 ± 0.10</div> <div>30~150 ± 0.15</div> <div>± 1°</div>		<div>ADAM TECH</div> <div>INTERCONNECTS</div> <div>909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</div>	
APPROVALS		TITLE	
DRAWN		DATE	
HR		11/12/18	
CHECKED		11/12/18	
CK			
APPROVED			
		POGO PIN CHARGING DOCKING, FEMALE, STRAIGHT	
		SIZE	
		X	
		PART NO.	
		PHR-C4777-02A-FVP-800	
		REV.	
		-	
		REF: S00170C	
		SCALE: NTS	
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PHR-C4777-02A-FVP-800](#)