



APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/22	
A		UPDATED TITLE	7/14/23	JJ/RC
B		ADDED SPEC.	7/26/23	LH/RC
C		UPDATED TITLE	8/4/23	JJ/RC



INSERTION LOSS(IN 50 ohm system according IEC/CISPR No.17)

— (common mode)
— (differential mode)



SPECIFICATIONS:

Electrical:

Voltage rating: 115/250 VAC

Current rating: 115/250 VAC: 10A RMS max

Operating frequency: 50/60Hz

Leakage Current: Each Line To Ground

@115VAC/60HZ 2.0uA max

@250VAC/50HZ 5.0uA max

Hipot Rating(For 1 Minute)

A. Line to Ground: 2,250 VDC

B. Line to Line: 500 VDC

IR: 50 Mohm @500 VDC Any Input or Output to Ground

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



, Medical Grade



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	Holes
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	JJ	11/7/22
CHECKED	RC	11/7/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE EMI/RFI POWER LINE FILTER, MEDICAL GRADE 115/250VAC 10A, WIRE LEADS W/ CHASSIS MOUNT	
SIZE X	PART NO. PLF-11E2-10A-W-R5
REF: S00205C	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PLF-11E2-10A-W-R5](#)