




APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-	9184	REDRAWN	10/21/08	
A	12318	REVISED DIM.	07/27/12	



CAP	BRASS	GOLD
FERRULE	BRASS	GOLD
DIELECTRIC	TEFLON	NONE
PIN	PHOS BRONZE	GOLD
BODY	BERYLLIUM	GOLD
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

**SPECIFICATIONS:**

Electrical:  
Nominal Impedance: 50 ohms  
Frequency range: 0–6 GHz  
Maximum working voltage: 335 VAC  
Insulation resistance: 1000 Mohm min  
Dielectric withstanding voltage: 1000 VAC rms min  
Environmental:  
Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 Ø.X ± .10  
.XX ± .020 Ø.XX ± .015  
.XXX ± .015 Ø.XXX ± .010

**ADAM TECH**  
909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

MCX MALE R/A CRIMP FOR RG174

APPROVALS		DATE	TITLE	
DRAWN	DY	10/21/08	SIZE	PART NO.
CHECKED			X	RF11-11-T-02-50-G
APPROVED			REF:	S00011T
			SCALE:	NTS
			SHEET	1 OF 1

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF11-11-T-02-50-G](#)