





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	8719	RELEASED	5/7/08	
A		REDRAWN	5/9/16	AY/NP



FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
RING	BE CU	GOLD
BODY	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency Range: DC-6 GHz

Normal Impedance: 50 ohm

Operating voltage: 170 Volts max.

Proof voltage: 500 Volts

VSWR: 1.3 max. @ 1 GHz

Temperature Rating:

Operating temperature: -55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-0214	
APPROVALS		DATE	
DRAWN	SS	5/7/08	
CHECKED			
APPROVED			
TITLE		RF CONNECTOR, TYPE MMCX, MALE CRIMP FOR RG174/U, 316/U, LMR-100, 50 OHM	
SIZE X	PART NO. RF12-06-T-02-50-G	REV. A	
REF: S00277T		SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-06-T-02-50-G](#)