





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	12124	RELEASED	4/24/12	
A	12124	REDRAWN	7/20/16	AY/SY



RECOMMENDED
CABLE STRIPPING DIM'S



FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD 3u"
RING	BE CU	GOLD
BODY	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency Range: DC–6 GHz

Normal Impedance: 50 ohm

Operating voltage: 170 Volts max.

Proof voltage: 500 Volts

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	4/24/12
CHECKED	NP	4/24/12
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908–687–5000 Fax: 908–687–0214

TITLE
RF CONNECTOR, TYPE MMCX, MALE CRIMP
FOR RG178/U, 50 OHM

SIZE X	PART NO. RF12-06-T-21-50-G	REV. A
REF: S00277T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-06-T-21-50-G](#)