


Rev	AWO #	Description	Date	Appr
-	9468	RELEASED	4/10/09	

APPROVED: _____

DATE: _____ TITLE: _____



PIN	Be Cu	GOLD
INSULATOR	TEFLON	NONE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
 Nominal Impedance: 50 ohms
 Frequency range: 0–6 GHz
 Working Voltage: 170 VRMS max.
 Dielectric Withstanding Voltage: 500 VRMS min.
 Contact Resistance: 5 Milliohms max. (Center Contact)
 2.5 Milliohms max. (Outer Contact)
 Insulator Resistance: 1000 Megohms min.
 Environmental:
 Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

MMCX JACK FOR PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				TITLE			
APPROVALS				DATE			
DRAWN		DY		4/10/09			
CHECKED							
APPROVED							
X				SIZE PART NO.			
REF: S00011T				REV.			
SCALE: NTS				SHEET 1 OF 1			
RF12-07-T-00-50-G				-			
MMCX JACK FOR PCB							
909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710							
ADAM TECH							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-07-T-00-50-G](#)