

6

5

4

3

2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/2/15	

APPROVED: _____


DATE: _____ TITLE: _____

D

D

C

C



B

B

CONTACT PIN	BE CU	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

Working Voltage: 170 VOLTS Max

Proof Voltage: 500 VOLTS

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



A

A

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		Holes	
.X ± .10	ØX ± .10	TITLE	
.XX ± .020	ØXX ± .015	RF CONNECTOR, TYPE MMCX ST. JACK,	
.XXX ± .015	ØXXX ± .010	50 OHM, PCB MOUNT	
APPROVALS		DATE	
DRAWN	AY	9/2/15	
CHECKED	AC	9/2/15	
APPROVED			
REF: S00277	SCALE: NTS	SHEET 1 OF 1	REV. -

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-07B-T-00-50-G](#)