




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/2/15	
A		ADDED TOLERANCE	10/29/15	
B		UPDATED INSULATOR SHAPE	11/3/15	HR/TW
C		UPDATE PLATE SPECIFICATION	12/11/15	HR/TW



RECOMMENDED PCB LAYOUT

PIN	BERYLLIUM COPPER	30u" GOLD
INSULATOR	TEFLON	
BODY	BRASS	GOLD FLASH
ITEM NAME	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

SWR: 1.25 max

Temperature Rating:

Operating temperature: –65°C to +165°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES

.X	$\pm .10$	$\phi .X$	$\pm .10$
.XX	$\pm .020$	$\phi .XX$	$\pm .015$
.XXX	$\pm .015$	$\phi .XXX$	$\pm .010$

APPROVALS DATE

DRAWN	HR	10/2/15
CHECKED	TW	10/2/15
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE RF CONNECTOR, TYPE MMCX ST. JACK,
 50 OHM, PCB MOUNT

SIZE X	PART NO. RF12-07D-T-00-50-G	REV. C
REF: S00049T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-07D-T-00-50-G](#)