


Rev	AWO #	Description	Date	Appr
-		RELEASED	9/13/11	

APPROVED: _____

DATE: _____ TITLE: _____



FERRULE	BRASS	GOLD
FERRULE	BRASS	GOLD
INSULATOR	POM	NONE
BODY	BRASS	GOLD
LINK LOCK	BE OU	GOLD
INSULATOR	TEFLON	NONE
CONTACT	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: 0–16 GHz

Working Voltage: 170 VRMS max.

Dielectric Withstanding Voltage: 500 VRMS min.

Contact Resistance: 5 Milliohms max. (Center Contact)

2.5 Milliohms max. (Outer Contact)

Insulator Resistance: 1000 Megohms min.

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-0214

TITLE

RF CONNECTOR, TYPE MMCX, TEFLON, RG174
50 OHMS, GOLD PLATED BODY CONTACT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED			
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	TW	9/13/11	
CHECKED	AY	9/13/11	
APPROVED			
SIZE	PART NO.	REV.	
X			
REF:	S00049T	SCALE:	NTS
SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-15-T-02-50-G](#)