

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

5/12/16

D




D

C

C

B

B



RECOMMENDED PCB LAYOUT

COVER TAPE	PI	AMBER
CONTACT PIN	BERYLLIUM COPPER	GOLD
INSULATOR	PTFE	WHITE
BODY	BRASS	GOLD
ITEM NAME	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 Ohms

Frequency range: DC-6 GHz

Working Voltage: 170 V max

Proof Voltage: 500 V

Temperature Rating:

Operating temperature: -55°C to +155°C

Environmental:

Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DATE

DRAWN

HR

5/12/16

CHECKED

LW

5/12/16

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
RF CONNECTOR, TYPE MMCX ST. JACK,
50 OHM, SURFACE MOUNT

SIZE

X

PART NO.

RF12-41-T-00-50-G

REV.

-

REF: S00277T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1

A

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF12-41-T-00-50-G](#)