






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/27/07	
A		REDRAWN	11/04/10	
B		REMOVE NUT & WASHER	12/01/10	
C		UPDATE DRAWING	5/6/15	AY/KW



RECOMMENDED PANEL CUTOUTS

INSULATOR	POM	NONE
BODY	ZINC ALLOY	NICKEL
CONTACT	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 75 ohms
Frequency range: DC~3G
VSWR: 1.3 Max
Working Voltage: 500 VRMS @ Sea level
Insulator Resistance: 5000 Megohms min.
Temperature Rating:
-55°C to +155°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

75 OHMS BNC R/A PCB/PANEL
MOUNT JACK, METAL BODY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010										ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710																			
APPROVALS										DATE										TITLE									
DRAWN					SLS					12/27/07					SIZE					PART NO.					REV.				
CHECKED															X					RF1-01-P-00-75-M					C				
APPROVED															REF: S00720C					SCALE: NTS					SHEET 1 OF 1				
75 OHMS BNC R/A PCB/PANEL MOUNT JACK, METAL BODY																													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-01-P-00-75-M](#)