


Rev	AWO #	Description	Date	Appr
-		RELEASED	8/29/07	
A		REDRAWN	02/08/13	

APPROVED: _____
DATE: _____ TITLE: _____
THE PART TO WITHSTAND THE HIGHER TEMPERATURE SOLDERING PROFILE




FIXTURE	BRASS	TIN
CENTER PIN	PHOSPHOR BRONZE	GOLD
CONTACT WIRE	BRASS	TIN
INSULATOR	PP	NONE
INSULATOR	POM	NONE
BODY	ZINC ALLOY	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS

Electrical:
Nominal Impedance: 50 Ohms
Frequency Range: 0 – 4 GHz
Maximum Peak Voltage: 500V
Insulation Resistance: 5000 Mohms min @ 500 VDC
Dielectric Withstanding Voltage: 1500 VAC rms.
Environmental:
Lead free, RoHS compliant.



RECOMMENDED PCB HOLE



A

B

C

D

A

B

C

D

ADAM TECH

909 Ratway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: BNC CONNECTOR, RIGHT ANGLE
50 OHMS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010	APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	SS	8/29/07	X	RF1-01A-P-00-50-M	A
CHECKED					
APPROVED					

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-01A-P-00-50-M](#)