






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/15	
A		ADDED DIM.	11/3/15	AY/SY



RECOMMENDED
PANEL CUTOUT



RECOMMENDED PCB LAYOUT

BODY	ZINC	NICKEL
CENTER CONTACT	BRASS	GOLD
LEAD	IRON	GOLD
FIXED FOOTREST	IRON	NICKEL
INSULATOR	POM	WHITE
FIXED MOUNT	ABS	WHITE
WASHER	BRASS	NICKEL
HEX NUT	BRASS	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 75 ohms

Frequency range: DC~3G

VSWR: 1.3 max.

Working Voltage: 500 VRMS @ Sea level

Insulator Resistance: 5000 Megohms min.

Temperature Rating:

-55°C to +155°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	5/11/15
CHECKED	MW	5/11/15
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

RIGHT ANGLE BNC CONNECTOR, 75 OHM

SIZE

X

PART NO.

RF1-01E-D-00-75

REV.

A

REF: S00128C

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-01E-D-00-75](#)