





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/05/08	
A		REVISED SPEC.	10/25/11	



SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0-4 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1,500 VRMS min.
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710
BNC MALE CRIMP

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	DY	8/05/08	RF1-03-D-01-50	A
CHECKED				
APPROVED				

REF: S00049T SCALE: NTS SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-03-D-01-50](#)