

6

5

4

3



2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/19/05	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



NO	DESCRIPTION	MATERIAL	FINISH	QTY
3	SLEEVE	BRASS	NICKEL	1
2	CENTER CONTACT BODY	BRASS	GOLD	1
	WASHER	ZINC	NICKEL	1
	WASHER	IRON	NICKEL	1
	SPRING	65Mn	NONE	1
1	DUT CONTACT	ZINC	NICKEL	1
	RUBBER WASHER	PVC	NONE	1
	INSULATOR	POM	NONE	1
	SHELL	ZINC	NICKEL	1

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X  $\pm .10$   $\varnothing$ .X  $\pm .10$   
.XX  $\pm .020$   $\varnothing$ .XX  $\pm .015$   
.XXX  $\pm .015$   $\varnothing$ .XXX  $\pm .010$

APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

**ADAM TECH**  
909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710  
BNC MALE CRIMP

ELECTRICAL:

Frequency range: 0-4 GHz  
Voltage rating: 500 Volts AC  
VSWR: 1.2 max 0-2 GHz  
Impedance: 75 OHMS  
Environmental:  
Lead free, RoHS compliant.



SIZE	PART NO.	REV.
X	RF-1-03-D-04-75	-
REP:	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-03-D-04-75](#)