

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/12/09	

6

5

4




3

2

1

APPROVED: _____

DATE: _____ TITLE: _____



NO	DESCRIPTION	MATERIAL	FINISH	QTY
9	GASKET	RUBBER	ORANGE	1
8	RETAINING RING	SK-5	NICKEL	1
7	SPRING	SK-5	NICKEL	1
6	WASHER	IRON	NICKEL	1
5	SHELL	BRASS	NICKEL	1
4	FERRULE	BRASS	NICKEL	1
3	DIELECTRIC	DELIN	NONE	1
2	PIN	BRASS	GOLD	1
1	BODY	BRASS	NICKEL	1

SPECIFICATIONS:

Electrical:
Impedance: 50 ohms
Frequency range: 0-4 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Ratway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC MALE CRIMP FOR H155 LMR240

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010		TITLE	
APPROVALS		DATE	
DRAWN	DY	2/12/09	
CHECKED	CH	2/12/09	
APPROVED			
REF: S00011T		SCALE: NTS	
SHEET 1 OF 1		REV. -	

ADAM TECH	
909 Railway Avenue, Union, NJ 07083	
Phone: 908-687-5000 Fax: 908-687-5710	
BNC MALE CRIMP FOR H155 LMR240	

SIZE	PART NO.
X	RF1-03-D-20-50

A

B

C

D

A

B

C

D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-03-D-20-50](#)