

6

5

4

3

2


1

Rev	AWO #	Description	Date	Appr
-	9362	RELEASED	2/16/09	



APPROVED: _____

DATE: _____ TITLE: _____

D




C



B

FERRULE	BRASS	NICKEL	1
FERRULE	BRASS	NICKEL	1
SLEEVE	ABC	NONE	1
CONTACT PIN	BRASS	GOLD	1
WASHER	IRON	NICKEL	1
SPRING	65Mn	NONE	1
OUT CONTACT	ZINC	NICKEL	1
GASKET	PVC	NONE	1
INSULATOR	TEFLON	NONE	1
BODY	BRASS	NICKEL	1
SHELL	ZINC	NICKEL	1
DESCRIPTION	MATERIAL	FINISH	QTY



B

SPECIFICATIONS:

Electrical:

Impedance: 75 ohms

Frequency range: 0–4 GHz

Working Voltage: 500 VRMS max.

Dielectric Withstanding Voltage: 1500 VRMS min.

Contact Resistance: 3 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5000 Megohms min.

Environmental:

Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

BNC MALE CRIMP FOR RG179, 75 OHM

A

A



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH			
INCHES				909 Rahway Avenue, Union, NJ 07083			
HOLES				Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	Ø.X	± .10	TITLE BNC MALE CRIMP FOR RG179, 75 OHM			
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				REF: S00049T			
DRAWN	DY	2/16/09	DATE	SCALE: NTS			
CHECKED	CH	2/16/09		SHEET 1 OF 1			
APPROVED				REV: .			

6

5

4

3

2

1

SIZE PART NO.
X RF1-03-T-03-75

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-03-T-03-75](#)