


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/18/11	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Body: Zinc Alloy, Nickel plated
Contacts: Phosphor Bronze, Gold plated
Insulator: TPX

Electrical:
Nominal Impedance: 75 ohms
Frequency range: 0-1 GHz
Working Voltage: 500 VRMS max.
Dielectric Withstanding Voltage: 1500 VRMS min.
Contact Resistance: 3 Milliohms max. (Center Contact)
2 Milliohms max. (Outer Contact)
Insulator Resistance: 5000 Megohms min.
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLES			
.X	± .10	ØXX	±.10	ØXX	±.015		
.XX	± .020	ØXX	±.015	ØXX	±.015		
.XXX	± .015	ØXXX	±.010	ØXXX	±.010		
APPROVALS				DATE			
DRAWN	AY		10/18/11				
CHECKED	NP		10/18/11				
APPROVED							
				TITLE			
				BNC CONNECTOR, 75Ω			
				909 Railway Avenue, Union, NJ 07083			
				Phone: 908-687-5000 Fax: 908-687-5710			
				ADAM TECH			
				RECOMMENDED PCB LAYOUT			
</							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-95-T-00-75](#)