


6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/3/17	



GROUND CONTACT	COPPER ALLOY	GOLD
INNER CONTACT	COPPER ALLOY	GOLD
HOUSING	LCP UL94V-0	
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC~6 GHz

Nominal Impedance: 50 Ohms

Rated Voltage: AC 60Vrms

VSWR: 1.3 max. @ 0.1~3 GHz
1.4 max. @ 3~6 GHz

Temperature Rating:

Operating temperature: -40°C to +80°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		APPROVALS DRAWN AY 10/3/17 CHECKED MY 10/3/17 APPROVED		DATE 10/3/17		TITLE RF CONNECTOR, MICRO COAXIAL 50 OHMS, VERTICAL, TAPE & REEL		SIZE X		PART NO. RF20-01B-L-00-50-G-T/R		REV. -	
REF: S00291T		SCALE: NTS		SHEET 1 OF 1									

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF20-01B-L-00-50-G-T/R](#)