



APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_







Rev	AWO #	Description	Date	Appr
-		RELEASED	7/20/16	



RECOMMENDED CABLE STRIPPING DIMS



RECOMMENDED MOUNTING HOLE



HEX NUT	BRASS	GOLD
WASHER	BRASS	GOLD
O-RING	SILICONE	RED
FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
INSULATOR	PTFE	WHITE
BURREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

**SPECIFICATIONS:**

Electrical:

Frequency range: DC-6 GHz

Nominal Impedance: 50 Ohms

Working Voltage: 250 VOLTS max

Proof Voltage: 750 VOLTS

VSWR : 1.3 Max @ 1 GHz

Temperature Rating:

Operating temperature: -65°C to +165°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 Ø.X ± .10  
.XX ± .020 Ø.XX ± .015  
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	7/20/16
CHECKED	SY	7/20/16
APPROVED		

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
RF CONNECTOR, SMA JACK STR BULKHEAD  
RG-174/U, 316/U, LMR-100

SIZE X	PART NO. RF2-06A-T-02-50-G	REV. -
REF: S00277T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF2-06A-T-02-50-G](#)